

Vertical laminar air flow cabinet, 900 wide

CONFORMIDAD

EN 61010-1, EN 61326-1, EN 61000-6-3

ADVANTAGES

SINO TAMBIÉN...

- Low noise fan
- High intensity of light
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- White walls for a glare-free brightness
- Easy replacement of the filters
- Electronic compartment located outside the contaminated area
- Microprocessor control system with digital display for airflow velocity
- Audible and visual alarm in case of airflow defect



CARACTERISTICAS TECNICAS

Modelo	FLV09	Caudal de aire (m3/h)	2150
Conformidad	EN 61010-1, EN 61326-1, EN 61000-6-3	Tensión (voltios)	0.99999
Dimensiones de envío alt x anc x pro (mm)	1500 x 1150 x 850	Potencia eléctrica (vatios)	760
Velocidad del aire (m/s)	0,4	Código Aduanero	84146011
Tensión (voltios)	220		

PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for FLV09 (Réf : FACFLV09)
- Support stand for FLV09 and PSM9 (Réf : TH09)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Peso (kg)
FLV09	1345 x 1060 x 795	620 x 890 x 630	165.00