

## Vertical laminar air flow cabinet, 900 wide

### CONFORMIDAD

EN 61010-1, EN 61326-1, EN 61000-6-3

### ADVANTAGES

#### SINO TAMBIÉN...

- Low noise fan
- High intensity of light
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- White walls for a glare-free brightness
- Easy replacement of the filters
- Electronic compartment located outside the contaminated area
- Microprocessor control system with digital display for airflow velocity
- Audible and visual alarm in case of airflow defect



### CARACTERISTICAS TECNICAS

Modelo	<b>FLV09</b>	Caudal de aire (m3/h)	<b>2150</b>
Conformidad	<b>EN 61010-1, EN 61326-1, EN 61000-6-3</b>	Tensión (voltios)	<b>0.99999</b>
Dimensiones de envío alt x anc x pro (mm)	<b>1500 x 1150 x 850</b>	Potencia eléctrica (vatios)	<b>760</b>
Velocidad del aire (m/s)	<b>0,4</b>	Código Aduanero	<b>84146011</b>
Tensión (voltios)	<b>220</b>		

### PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for FLV09 (Réf : FACFLV09)
- Support stand for FLV09 and PSM9 (Réf : TH09)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Peso (kg)
FLV09	1345 x 1060 x 795	620 x 890 x 630	165.00