

Class II Microbiological safety cabinet, 1200 mm wide

CONFORMIDAD

EN 12469

ADVANTAGES

- Convenient for micro-organisms
- Low noise fan
- High intensity of light
- White walls for a glare-free brightness
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- Easy replacement of the filters
- Ergonomic armrest for long periods of handling
- Electronic compartment located outside the contaminated area
- Alarms for : power failure, control system failure, open window, low and high airflow velocity, filters clogged

SINO TAMBIÉN...



CARACTERISTICAS TECNICAS

Modelo	PSM12	Tensión (voltios)	220
Conformidad	EN 12469	Tensión (voltios)	0.99999
Dimensiones de envío alt x anc x pro (mm)	1540 x 1450 x 850	Potencia eléctrica (vatios)	1860
Velocidad del aire (m/s)	0,4	Código Aduanero	84146011

PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for PSM12 (Réf : FACPSM12)
- Support stand for FLV12 and PSM12 (Réf : TH12)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Peso (kg)
PSM12	1400 x 1360 x 795	650 x 1190 x 600	220.00