

# Class II Microbiological safety cabinet, 1200 mm wide

## CONFORMIDAD

EN 12469

## ADVANTAGES

- Convenient for micro-organisms
- Low noise fan
- High intensity of light
- White walls for a glare-free brightness
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- Easy replacement of the filters
- Ergonomic armrest for long periods of handling
- Electronic compartment located outside the contaminated area
- Alarms for : power failure, control system failure, open window, low and high airflow velocity, filters clogged

## SINO TAMBIÉN...



## CARACTERISTICAS TECNICAS

Modelo	<b>PSM12</b>	Tensión (voltios)	<b>220</b>
Conformidad	<b>EN 12469</b>	Tensión (voltios)	<b>0.99999</b>
Dimensiones de envío alt x anc x pro (mm)	<b>1540 x 1450 x 850</b>	Potencia eléctrica (vatios)	<b>1860</b>
Velocidad del aire (m/s)	<b>0,4</b>	Código Aduanero	<b>84146011</b>

## PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for PSM12 (Réf : FACPSM12)
- Support stand for FLV12 and PSM12 (Réf : TH12)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Peso (kg)
PSM12	1400 x 1360 x 795	650 x 1190 x 600	220.00