

Cassettone di ventilazione con motore ATEX

CONFORMIDAD

ATEX Zone 2

ADVANTAGES

- CE certified
- ATEX zone II certified
- ATEX certified

SINO TAMBIÉN...

- Lighting control allowing to survey the proper working of the fan
- Easy and aesthetic installation
- Allow the extraction of the chemicals vapors contained in the cabinet



CARACTERISTICAS TECNICAS

Modelo	CMAT	Dimensiones de envío alt x anc x pro (mm)	700 x 500 x 500
Conformidad	ATEX Zone 2	Código Aduanero	84145940

PRODUITS COMPLÉMENTAIRES

- Filtro rotondo ha carbone attivo polivalente - for filtration box type CDF or cabinet AF10 (Réf : CDFCORG)
- Filtro rotondo ha carbone attivo Formolo - for filtration box type CDF or cabinet AF10 (Réf : CDFFOR)
- Filtro rotondo ha carbone attivo organico - for filtration box type CDF or cabinet AF10 (Réf : CDFORG)
- Collana di serraggio in plastica (Réf : CDS100)
- Uscita di ventilazione, diam. 100 mm (Réf : CHJ)
- Tubo agile, diam. 100 mm, il metro, (Réf : KL100)
- Kit di raccordo per cassetto (Réf : KRC)

Modelo	Dimensiones exteriores alt x anc x pro (mm)	Dimensiones interiores alt x anc x pro (mm)	Peso (kg)
CMAT	305 x 650 x 285		18.00