

# Cassettone di ventilazione con motore ogni ATEX

## CONFORMIDAD

ATEX Zone 2

## ADVANTAGES

- CE certified
- ATEX zone II certified
- ATEX certified

## SINO TAMBIÉN...

- Lighting control allowing to survey the proper working of the fan
- Easy and aesthetic installation
- Allow the extraction of the chemicals vapors contained in the cabinet



## CARACTERISTICAS TECNICAS

|             |                    |                                           |                        |
|-------------|--------------------|-------------------------------------------|------------------------|
| Modelo      | <b>CTAT</b>        | Dimensiones de envío alt x anc x pro (mm) | <b>700 x 500 x 500</b> |
| Conformidad | <b>ATEX Zone 2</b> | Código Aduanero                           | <b>84145940</b>        |

## PRODUITS COMPLÉMENTAIRES

- Filtro rotondo ha carbone attivo polivalente - for filtration box type CDF or cabinet AF10 (Réf : CDFCORG)
- Filtro rotondo ha carbone attivo Formolo - for filtration box type CDF or cabinet AF10 (Réf : CDFFOR)
- Filtro rotondo ha carbone attivo organico - for filtration box type CDF or cabinet AF10 (Réf : CDFORG)
- Collana di serraggio in plastica (Réf : CDS100)
- Uscita di ventilazione, diam. 100 mm (Réf : CHJ)
- Tubo agile, diam. 100 mm, il metro, (Réf : KL100)
- Kit di raccordo per cassetto (Réf : KRC)

| Modelo | Dimensiones exteriores alt x anc x pro (mm) | Dimensiones interiores alt x anc x pro (mm) | Peso (kg) |
|--------|---------------------------------------------|---------------------------------------------|-----------|
| CTAT   | 305 x 650 x 285                             |                                             | 18.00     |