

Class II Microbiological safety cabinet, 1200 mm wide

CONFORMITÀ

EN 12469

ADVANTAGES

- Convenient for micro-organisms
- Low noise fan
- High intensity of light
- White walls for a glare-free brightness
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- Easy replacement of the filters
- Ergonomic armrest for long periods of handling
- Electronic compartment located outside the contaminated area
- Alarms for : power failure, control system failure, open window, low and high airflow velocity, filters clogged

MA ANCHE...



CARATTERISTICHE TECNICHE

Modello	PSM12	Voltaggio (volt)	220
Conformità	EN 12469	Voltaggio (volt)	0.99999
Dimensioni di spedizione HxWxD (mm)	1540 x 1450 x 850	Potenza elettrica (W)	1860
Flusso d'aria (m/s)	0,4	Codice HS	84146011

PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for PSM12 (Réf : FACPSM12)
- Support stand for FLV12 and PSM12 (Réf : TH12)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Modello	Dimensioni esterne HxWxD (mm)	Dimensioni interne HxWxD (mm)	Peso (kg)
PSM12	1400 x 1360 x 795	650 x 1190 x 600	220.00