

Class II Microbiological safety cabinet, 900 mm wide

CONFORMITÀ


EN 12469

ADVANTAGES

- Convenient for micro-organisms

MA ANCHE...

- Low noise fan
- High intensity of light
- White walls for a glare-free brightness
- Smooth walls, rounded corners and no welds ; allowing easy cleaning and decontamination
- Easy replacement of the filters
- Ergonomic armrest for long periods of handling
- Electronic compartment located outside the contaminated area
- Alarms for : power failure, control system failure, open window, low and high airflow velocity, filters clogged



CARATTERISTICHE TECNICHE

Modello	PSM9	Voltaggio (volt)	0.99999
Conformità	EN 12469	Potenza elettrica (W)	1860
Flusso d'aria (m/s)	0,4	Codice HS	84146011
Voltaggio (volt)	220		

PRODUITS COMPLÉMENTAIRES

- Front enclosure with UV light for PSM9 (Réf : FACPSM09)
- Support stand for FLV09 and PSM9 (Réf : TH09)
- Gas valve with solenoid valve (Réf : VANGAZ)
- Vacuum valve (Réf : VANVID)

Modello	Dimensioni esterne HxWxD (mm)	Dimensioni interne HxWxD (mm)	Peso (kg)
PSM9	1390 x 1050 x 790	630 x 885 x 630	144.00