

# Ductless fume hood 1200 mm - 2 Modules - for clean room - one opening

## CONFORMITÀ

## ADVANTAGES

- CE certified
- NFX 15-211 compliant
- Storage of flammables, corrosives and toxics

## MA ANCHE...

- Easy replacement of the active coal filter
- Low acoustic level
- Front control window to see immediately the filter
- NFX 15-211 compliant
- Delivered ready to use
- Lighting control allowing to survey the proper working of the fan
- Holes for the cables and fluid going through
- Glass side walls
- Ergonomic hand traps or trapezoidal opening



## CARATTERISTICHE TECNICHE

Modello	<b>H122Z+2CH</b>	Contaore	<b>included</b>
Flusso d'aria (m/s)	<b>0,4 - 0,6</b>	Presa di campionamento	<b>included</b>
Voltaggio (volt)	<b>220-240</b>	Parete posteriore trasparente	<b>included</b>
Flusso (m3/h)	<b>170</b>	Piano lavoro in melamina	<b>Option</b>
Aperture passaggio cavi	<b>4</b>	Potenza elettrica (W)	<b>27</b>
Anemometro	<b>included</b>	Rumore dB (A)	<b>57.00</b>
Guida alle sostanze chimiche adsorbite	<b>included</b>	Codice HS	<b>84146000</b>

## PRODUITS COMPLÉMENTAIRES

- Filtro ha carbone attivo per vapori ammoniaci per sorbonne - for old fume hoods type 200, 201, 210 and 211 (Réf : AMM200)
- Filtro ha carbone attivo polivalente - for old fume hoods type 200, 201, 210 and 211 (Réf : CORG201)
- Filtro ha carbone attivo per formolo - for old fume hoods type 200, 201, 210 and 211 (Réf : FOR200)
- Filtro HEPA H14 per sorbonne tipo 200 (Réf : HEP200)
- Filtro ha carbone attivo per vapori organici - for old fume hoods type 200, 201, 210 and 211 (Réf : ORG200)
- Containment sump and melamine work-top for H12 (Réf : BB12)
- Containment sump and tempered glass work-top for H12 (Réf : BV12)
- Supporto per filtro HEPA H14 per sorbonnes rif. H201/H211 (Réf : SH200)

## OPTIONS

- Lighting for ductless fume hoods (Réf : LUMI)
- Table-cabinet for H12 (Réf : TA12)
- Trolley with adjustable shelf for H12 (Réf : TR12)
- Tubular table with feet for model H12 (Réf : TTF12)
- Tubular table with wheels for model H12 (Réf : TTR12)

Modello	Dimensioni esterne HxWxD (mm)	Dimensioni interne HxWxD (mm)	Peso (kg)
H122Z+2CH	1160 x 1200 x 750	935 x 1145 x 700	44.00