

# Ductless fume hood 1500 mm - 3 modules - for liquid - one opening

## CONFORMITÀ

NF X 15-211 Classe 1

## ADVANTAGES

- CE certified
- NF X 15-211 compliant
- Storage of flammables, corrosives and toxics

- Norma EN 17242

## MA ANCHE...

- Easy replacement of the active coal filter
- Low acoustic level
- Front control window to see immediately the filter
- NF X 15-211 compliant
- Delivered ready to use
- Interfaccia touchscreen FILTRALARME 5, funzionamento del sistema di ventilazione
- Holes for the cables and fluid going through
- Glass side walls



## CARATTERISTICHE TECNICHE

Modello	<b>H153Z+2C</b>	Contaore	<b>included</b>
Conformità	<b>NF X 15-211 Classe 1</b>	Presa di campionamento	<b>included</b>
Flusso d'aria (m/s)	<b>0,4 - 0,6</b>	Parete posteriore trasparente	<b>included</b>
Voltaggio (volt)	<b>220-240</b>	Piano lavoro in melamina	<b>option</b>
Flusso (m <sup>3</sup> /h)	<b>170</b>	Potenza elettrica (W)	<b>27</b>
Aperture passaggio cavi	<b>4</b>	Rumore dB (A)	<b>57.00</b>
Anemometro	<b>included</b>	Codice HS	<b>84146000</b>
Guida alle sostanze chimiche adsorbite	<b>included</b>		

## PRODUITS COMPLÉMENTAIRES

- Filtro ha carbone attivo per vapori organici - for old fume hoods type 200, 201, 210 and 211 (Réf : ORG200)
- Filtro ha carbone attivo polivalente - for old fume hoods type 200, 201, 210 and 211 (Réf : CORG201)
- Filtro ha carbone attivo per formolo - for old fume hoods type 200, 201, 210 and 211 (Réf : FOR200)
- Filtro ha carbone attivo per vapori ammoniaci per sorbonne - for old fume hoods type 200, 201, 210 and 211 (Réf : AMM200)
- Containment sump and melamine work-top for H15 (Réf : BB15)
- Containment sump and tempered glass work-top for H15 (Réf : BV15)

## OPTIONS

- Lighting for ductless fume hoods (Réf : LUMI)
- Table-cabinet for H15 (Réf : TA15)
- Trolley with adjustable shelf for H15 (Réf : TR15)
- Tubular table with wheels for model H15 (Réf : TTR15)
- Tubular table with feet for model H15 (Réf : TTF15)

Modello	Dimensioni esterne HxWxD (mm)	Dimensioni interne HxWxD (mm)	Peso (kg)
H153Z+2C	1160 x 1500 x 750	935 x 1445 x 700	54.00