

H092D+2CH



Ductless fume hood 900 mm - 2 Modules - for clean room - two openings

CONFORMITÀ

ADVANTAGES

- CE certified
- NF X 15-211 compliant
- Storage of flammables, corrosives and toxics

MA ANCHE...

- Easy replacement of the active coal filter
- Low acoustic level
- Front control window to see immediately the filter
- NF X 15-211 compliant
- Delivered ready to use
- Lighting control allowing to survey the proper working of the fan
- Glass side walls
- Ergonomic hand traps or trapezoidal opening



CARATTERISTICHE TECNICHE

| | | | |
|--|------------------|-------------------------------|-----------------|
| Modello | H092D+2CH | Contaore | included |
| Flusso d'aria (m/s) | 0,4 - 0,6 | Presa di campionamento | included |
| Voltaggio (volt) | 220-240 | Parete posteriore trasparente | included |
| Flusso (m ³ /h) | 170 | Piano lavoro in melamina | option |
| Aperture passaggio cavi | 4 | Potenza elettrica (W) | 63 |
| Anemometro | included | Rumore dB (A) | 60.00 |
| Guida alle sostanze chimiche adsorbite | included | Codice HS | 84146000 |

PRODUITS COMPLÉMENTAIRES

- Filtro ha carbone attivo per vapori ammoniaci per sorbonne - for old fume hoods type 200, 201, 210 and 211 (Réf : AMM200)
- Filtro ha carbone attivo polivalente - for old fume hoods type 200, 201, 210 and 211 (Réf : CORG201)
- Filtro ha carbone attivo per formolo - for old fume hoods type 200, 201, 210 and 211 (Réf : FOR200)
- Filtro HEPA H14 per sorbonne tipo 200 (Réf : HEP200)
- Filtro ha carbone attivo per vapori organici - for old fume hoods type 200, 201, 210 and 211 (Réf : ORG200)
- Supporto per filtro HEPA H14 per sorbonnes rif. H201/H211 (Réf : SH200)
- Containment sump and melamine work-top for H09 (Réf : BB09)
- Containment sump and tempered glass work-top for H09 (Réf : BV09)

OPTIONS

- Lighting for ductless fume hoods (Réf : LUMI)
- Table-cabinet for H09 (Réf : TA09)
- Trolley with adjustable shelf for H09 (Réf : TR09)
- Tubular table with feet for model H09 (Réf : TTF09)
- Tubular table with wheels for model H09 (Réf : TTR09)

| Modello | Dimensioni esterne HxWxD (mm) | Dimensioni interne HxWxD (mm) | Peso (kg) |
|-----------|-------------------------------|-------------------------------|-----------|
| H092D+2CH | 1160 x 900 x 750 | 935 x 845 x 700 | 34.00 |