

H184G+



Ductless fume hood 1800 mm - 4 Modules - Large opening

CONFORMITÀ

NF X 15-211 Classe 2

ADVANTAGES

- CE certified
- NF X 15-211 compliant
- Storage of flammables, corrosives and toxics

MA ANCHE...

- Easy replacement of the active coal filter
- Low acoustic level
- Front control window to see immediately the filter
- NF X 15-211 compliant
- Delivered ready to use
- Lighting control allowing to survey the proper working of the fan
- Holes for the cables and fluid going through
- Glass side walls
- Ergonomic hand traps or trapezoidal opening



CARATTERISTICHE TECNICHE

Modello	H184G+	Contaore	included
Conformità	NF X 15-211 Classe 2	Presa di campionamento	included
Flusso d'aria (m/s)	0,4 - 0,6	Parete posteriore trasparente	included
Voltaggio (volt)	220-240	Piano lavoro in melamina	Option
Flusso (m ³ /h)	170	Potenza elettrica (W)	27
Aperture passaggio cavi	4	Rumore dB (A)	57,00
Anemometro	included	Codice HS	84146000
Guida alle sostanze chimiche adsorbite	included		

PRODUITS COMPLÉMENTAIRES

- Filtro ha carbone attivo per vapori ammoniaci per sorbonne - for old fume hoods type 200, 201, 210 and 211 (Réf : AMM200)
- Filtro ha carbone attivo polivalente - for old fume hoods type 200, 201, 210 and 211 (Réf : CORG201)
- Filtro ha carbone attivo per formolo - for old fume hoods type 200, 201, 210 and 211 (Réf : FOR200)
- Filtro HEPA H14 per sorbonne tipo 200 (Réf : HEP200)
- Filtro ha carbone attivo per vapori organici - for old fume hoods type 200, 201, 210 and 211 (Réf : ORG200)
- Supporto per filtro HEPA H14 per sorbonnes rif. H201/H211 (Réf : SH200)
- Containment sump and melamine work-top for H18 (Réf : BB18)
- Containment sump and tempered glass work-top for H18 (Réf : BV18)

OPTIONS

- Lighting for ductless fume hoods (Réf : LUMI)
- Trolley with adjustable shelf for H18 (Réf : TR18)
- Tubular table with feet for model H18 (Réf : TTF18)
- Tubular table with wheels for model H18 (Réf : TTR18)
- Table-cabinet for H18 (Réf : TA18)

Modello	Dimensioni esterne HxWxD (mm)	Dimensioni interne HxWxD (mm)	Peso (kg)
H184G+	1240 x 1800 x 750	935 x 1745 x 700	70.00